

Product availability: Stock - Normally stocked in distribution facility

Price*: 152.00 USD

NATO products



Main

Commercial Status	Commercialised
Range of product	9050JCK
Product or component type	Timer
[In] rated current	10 A
Switch function	DPDT
Contacts type and composition	2 NO + 2 NC
Control circuit voltage	120 V AC
Maximum switching voltage	240 V AC
Mounting support	Socket
Pin number	8
Shape of pin	Tubular
Product certifications	CE CSA UL listed
Time delay type	On-delay
Time delay range	1...999 min 1...999 s 0.05...9.99 s 0.1...99.9 s 0.1...99.9 min

Ordering and shipping details

Category	21652 - 9050 JCK60, 70 PROGRAMMABLE TIMERS
Discount Schedule	CP2
GTIN	00785901053866
Nbr. of units in pkg.	1
Package weight(Lbs)	0.28
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0703 - Schneider Electric declaration of conformity

Contractual warranty

Period	18 months
--------	-----------