Product data sheet Characteristics

8501XDO40V62 RELAY 600VAC 10AMP NEMA +OPTIONS

Product availability: Stock - Normally stocked in distribution facility

Price*: 313.00 USD

Main	
Commercial Status	Commercialised
Range of product	8501X
Relay type	Control
Product or component type	Relay
[In] rated current	5 A DC 10 A AC
Contacts type and composition	4 NO 4 standard contact cartridges
Control circuit voltage	115/125 V DC
Mounting support	Panel
Ambient air temperature for operation	-40160 °F
Electrical connection	Screw clamp terminals
Product certifications	CE CSA

UL listed

21 ms drop-out 37 ms pick-up

Ordering and shipping details

Category	21157 - 8501 XDO (DC)	
Discount Schedule	CP2	
GTIN	00785901548737	
Nbr. of units in pkg.	1	
Package weight(Lbs)	3.39	
Product availability	Stock - Normally stocked in distribution facility	
Returnability	Υ	
Country of origin	MX	

Operating time

Offer Sustainability

Sustainable offer status	Not Green Premium product	
RoHS	Will be Compliant on 3Q2014	
REACh	Reference not containing SVHC above the threshold	

Contractual warranty

Contractadi Warranty	
Period	18 months