



Main

Range	ClimaSys CR
Category	Ultra thin resistance heater
Rated power in W	195 W
Input voltage	240 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

Complementary

Operating position	Horizontal Vertical
Ambient air temperature for operation	-60...70 °C
Temperature setting range	-40...70 °C
Material	Silicone rubber
Height	External : 400 mm
Width	External : 650 mm
Depth	External : 1.6 mm
Device composition	Fixing accessories 4 clip-on nuts 4 Telequick nuts 6 plastic spacers 6 self-adhesive Velcro pads
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By 4 screws
Mounting support	DIN rail Telequick mounting plate Adhesive Velcro Standard mounting plate