

Product data sheet

Characteristics

6T2F

TRANSFORMER DRY 3PH 6KVA

480V-208Y/120V

Product availability: Stock - Normally stocked in distribution facility

Price*: 2310.00 USD



Main

Commercial Status	Commercialised
Product or component type	Dry Sealed Transformer
Box number	12C
NEMA degree of protection	NEMA 3R
Insulation temperature	356 °F (180 °C)
Network number of phases	3 phases
Primary voltage	480 V delta
Rated power in VA	6 kVA
Secondary voltage	208Y/120 V
Number of tap-offs	2 5 % FCBN
Temperature rise	115 °C

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901359470
Nbr. of units in pkg.	1
Package weight(Lbs)	165.00
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative