



Product availability: Stock - Normally stocked in distribution facility



### Main

Commercial Status	Commercialised
Product or component type	Single Unit Manual Switch
Range of product	K
[In] rated current	30 A
Product certifications	CE CSA UL listed
Cable entry	0.5" and 0.75" knock-outs (top and bottom)
NEMA degree of protection	NEMA 1 painted sheet steel standard size
Motor power hp	1.5 hp 230 V DC 2 hp 115 V DC 1 hp 90 V DC 3 hp 575 V AC 3 hp 460 V AC 2 hp 230 V AC 2 hp 115 V AC
[Ue] rated operational voltage	230 V DC 600 V AC
Poles description	2P
Control type	Toggle
Network number of phases	1 phase
Local signalling	Red indicator 115 V
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals

### Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901554486
Nbr. of units in pkg.	3
Package weight(Lbs)	0.87
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------