Source Audio Power Amplifier With Built-in DAC

The **Source Audio Power Amplifier With Built-in DAC** is a power amplifier with 15W of output in STEREO mode. Not only does it have outstanding musical performance, but it also has a capacity enough to drive most of the high-end speakers in the market.

PARTS SUPPLIED:

- Amplifier Box (1)
- Power Supply (1)

SPECIFICATIONS

Speaker Audio Power Amplifier:

- Amplifier Type: Stereo Class-D
- Output power: 15W(rms) per channel (@ RL=4 ohm)
- THD+N :0.06 % (@ RL=8 ohm, f = 1 kHz)
- Minimum Load Resistance: 4 ohm
- Includes Speaker Protection circuit

Earphone Audio Power Amplifier:

- Output power: 105mW(rms) per channel
- THD+N :0.05 % (@ RL=16 ohm, f = 1 kHz)
- Minimum Load Resistance: 16 ohm

Digital to Analog Converter (DAC):

- Digital Input Type: Coaxial & Optical
- Support Digital Audio Format: LPCM
- Input Impedance: 75 ohms
- Frequency Response: 32 - 192KHz sample rate

PHYSICAL SPECIFICATIONS

- Dimensions:205.4L x 108.6W x 26H mm
- Weight: 468g

INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronics Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Setup Diagram