



Prokit's Industries CO., LTD.

5F, No.7, Lane 130,
Ming-Chung Rd., Hsin-Tien Dist,
New Taipei City, Taiwan, R.O.C. Post code: 23114
Tel: 886-2-2218-3233; Fax: 886-2-2218-2722
<http://www.prokits.com.tw> Email: sales-c@mail.prokits.com.tw

PRODUCT SPECIFICATION

Item #	Farnell UK Item #	Description	MOQ	Carton Quantity	N.W	G.W	CUFT
1PK-1700NC (W/ UK plug)	1494158	Electronic Master Kit (220V, Metric)	10 set	2 set	17 kgs	18 kgs	1.93



*** Picture for reference only. All specifications are subject to change by supplier. ***

Spec.

Item No.	Description
8PK-108T	Reverse Action Tweezer
8PK-154	Brush
903-132C-G	Utility Component Storage Box
908-313B	Heavy Duty Wire Stripper / Crimper (Metric)
908-607	Alignment Tool (200 mm / 2.0 mm)
908-609	IC Extractor
9400-M5	PRO-SOFT Screwdriver 5 mm NUT
9400-M6	PRO-SOFT Screwdriver 6 mm NUT
9401A	PRO-SOFT Slotted Screwdriver (3.2 x 75 mm)
9401B	PRO-SOFT Phillips Screwdriver (#0 x 75 mm)
9402A	PRO-SOFT Slotted Screwdriver (5.0 x 75 mm)
9402B	PRO-SOFT Phillips Screwdriver (#1 x 75 mm)
9407A	PRO-SOFT Slotted Screwdriver (6.0 x 100 mm)
9407B	PRO-SOFT Phillips Screwdriver (#2 x 100 mm)
9C004	Oil Can
9DK-2039	Utility Knife with 3 Spare Blades
9DK-2040	Measuring Tape (L=3M / 10FT)
9H002	7 PCS Folding Type Hex Key Set (Metric)
9H003	3 Prong Holder
9H021	6 PCS Open-end Wrench Set
9H026	Adjustable Wrench (150mm)
9IT	PVC Insulated Tape
9K002	Stainless Scissors
8PK-605A	5 PCS Needle File Set
9PN-P010	Slip-channel Pump Plier 254 mm
9PM-736	Long Nose Plier 135 mm
9PM-737	Diagonal Cutting Plier 113 mm
9PK-051DS	Dual Color Lineman's Plier 205 mm
9PM-755	Bent Nose Plier 130 mm
9P708	Side Cutting Plier 150 mm
9PK-709DS	Dual Color Long Nose Plier
9PK-031B	Desoldering Wick
9PK-2061	6 PCS Electronic Screwdriver Set

9PK-362D	Soldering Iron Stand with Sponge
9PK-366N-G	Desoldering Pump
9S002A	Soldering Aid Tool
9S002B	Soldering Aid Tool
9S002C	Soldering Aid Tool
9S004	Heat Sink
9TC-700	Carrying Tool Case
9PK-1700N-P	Pallet for 1PK-1700N
9PK-1700N-TP	Top Pallet for 1PK-1700N
9SD-220A	PRO-SOFT Slotted Screwdriver (6.0 x 40 mm)
9SD-220B	PRO-SOFT Phillips Screwdriver (#2 x 40 mm)
PD-2606	Heavy Duty Curved-claw Hammer
9S003N	Parts Tube
9MS-391	Inspection Mirror
9SN-310G	Solder Core (Sn 99.3%, Cu 0.7%)
8PK-S120NC-40	40W Soldering Iron, CE & RoHS compliance (480°C±10%)

Individual packing: Color box

Measurement of Tool Case (450 x 325 x 132 mm), Carton (480 x 340 x 380 mm)

~ THE END ~