

HIS-Service Station

This sturdy Service Station contains up to 5 dispensers. It can be put on a bench or mounted to a wall. A special cutter is included and makes it easy to cut the tubing length as desired

| Technical Table | |
|-----------------|---|
| Article-No. | Description |
| 365-30100 | HIS-Service Station incl. cutter , contents: 5 dispensers HIS-3 (shrink ratio: 3:1), black, sizes are as follows: HIS-3/1, HIS-6/2, HIS-12/4 (2 pcs.), HIS-24/8 |
| 365-20000 | HIS-Service Station incl. cutter , contents: 5 dispensers HIS-Pack (shrink ratio: 2:1), black, sizes are as follows: HIS-1/8, HIS-3/16, HIS-1/4, HIS-3/8, HIS 1/2 and one RiteOn Starter Pack |
| 300-30000 | HIS-Service Station incl. cutter, empty |



HIS-Service Station contains 5 dispensers and a special cutter.

HIS-Pack

Features and Benefits

- E-beam Crosslinked Polyolefin, thin-wall and flexible
- Shrink ratio 2:1
- Available in colours: black, red, blue, transparent and yellow/green.
- 10 sizes from 1.2mm to 25.4mm
- Handy dispenser box including table with full range of applications

Application

- General purpose electrical insulation
- Protection against corrosion and mechanical abrasion



HIS-A.

| Material Data | |
|-------------------------------------|---|
| Material | Polyolefin, Cross-linked (POX) |
| Shrink Ratio | 2:1 |
| Longitudinal change after shrinkage | -5% max. |
| Minimum Shrink Temperature | +120 °C |
| Operating Temperature | -55 °C to +135 °C |
| Dielectric Strength | 25 kV/mm according to IEC 60684 P2 |
| Flammability | ASTM D2671 |



HIS-Pack

Technical Table

| Article-No. | Type | Supplied Ø D | Recov. Ø d | Wall (WT) nom. | Pack Cont. (m) | Colour |
|-------------|---------------|-----------------|---------------|-------------------|-------------------|---------------------|
| 300-30120 | HIS-Pack-3/64 | 1.2 | 0.6 | 0.4 | 10 | Black (BK) |
| 300-30122 | HIS-Pack-3/64 | 1.2 | 0.6 | 0.4 | 10 | Red (RD) |
| 300-30123 | HIS-Pack-3/64 | 1.2 | 0.6 | 0.4 | 10 | Transparent (CL) |
| 300-30126 | HIS-Pack-3/64 | 1.2 | 0.6 | 0.4 | 10 | Blue (BU) |
| 300-30160 | HIS-Pack-1/16 | 1.6 | 0.8 | 0.4 | 10 | Black (BK) |
| 300-30162 | HIS-Pack-1/16 | 1.6 | 0.8 | 0.4 | 10 | Red (RD) |
| 300-30163 | HIS-Pack-1/16 | 1.6 | 0.8 | 0.4 | 10 | Transparent (CL) |
| 300-30166 | HIS-Pack-1/16 | 1.6 | 0.8 | 0.4 | 10 | Blue (BU) |
| 300-30240 | HIS-Pack-3/32 | 2.4 | 1.2 | 0.5 | 10 | Black (BK) |
| 300-30242 | HIS-Pack-3/32 | 2.4 | 1.2 | 0.5 | 10 | Red (RD) |
| 300-30243 | HIS-Pack-3/32 | 2.4 | 1.2 | 0.5 | 10 | Transparent (CL) |
| 300-30246 | HIS-Pack-3/32 | 2.4 | 1.2 | 0.5 | 10 | Blue (BU) |
| 300-30320 | HIS-Pack-1/8 | 3.2 | 1.6 | 0.5 | 10 | Black (BK) |
| 300-30322 | HIS-Pack-1/8 | 3.2 | 1.6 | 0.5 | 10 | Red (RD) |
| 300-30323 | HIS-Pack-1/8 | 3.2 | 1.6 | 0.5 | 10 | Transparent (CL) |
| 300-30326 | HIS-Pack-1/8 | 3.2 | 1.6 | 0.5 | 10 | Blue (BU) |
| 300-30327 | HIS-Pack-1/8 | 3.2 | 1.6 | 0.5 | 10 | Green-Yellow (GNYE) |
| 300-30480 | HIS-Pack-3/16 | 4.8 | 2.4 | 0.5 | 10 | Black (BK) |
| 300-30482 | HIS-Pack-3/16 | 4.8 | 2.4 | 0.5 | 10 | Red (RD) |
| 300-30483 | HIS-Pack-3/16 | 4.8 | 2.4 | 0.5 | 10 | Transparent (CL) |
| 300-30486 | HIS-Pack-3/16 | 4.8 | 2.4 | 0.5 | 10 | Blue (BU) |
| 300-30487 | HIS-Pack-3/16 | 4.8 | 2.4 | 0.5 | 10 | Green-Yellow (GNYE) |
| 300-30640 | HIS-Pack-1/4 | 6.4 | 3.2 | 0.6 | 5 | Black (BK) |
| 300-30642 | HIS-Pack-1/4 | 6.4 | 3.2 | 0.6 | 5 | Red (RD) |
| 300-30643 | HIS-Pack-1/4 | 6.4 | 3.2 | 0.6 | 5 | Transparent (CL) |
| 300-30646 | HIS-Pack-1/4 | 6.4 | 3.2 | 0.6 | 5 | Blue (BU) |
| 300-30647 | HIS-Pack-1/4 | 6.4 | 3.2 | 0.6 | 5 | Green-Yellow (GNYE) |
| 300-30950 | HIS-Pack-3/8 | 9.5 | 4.7 | 0.6 | 5 | Black (BK) |
| 300-30952 | HIS-Pack-3/8 | 9.5 | 4.7 | 0.6 | 5 | Red (RD) |
| 300-30953 | HIS-Pack-3/8 | 9.5 | 4.7 | 0.6 | 5 | Transparent (CL) |
| 300-30956 | HIS-Pack-3/8 | 9.5 | 4.7 | 0.6 | 5 | Blue (BU) |
| 300-30957 | HIS-Pack-3/8 | 9.5 | 4.7 | 0.6 | 5 | Green-Yellow (GNYE) |
| 300-31270 | HIS-Pack-1/2 | 12.7 | 6.4 | 0.6 | 5 | Black (BK) |
| 300-31272 | HIS-Pack-1/2 | 12.7 | 6.4 | 0.6 | 5 | Red (RD) |
| 300-31273 | HIS-Pack-1/2 | 12.7 | 6.4 | 0.6 | 5 | Transparent (CL) |
| 300-31276 | HIS-Pack-1/2 | 12.7 | 6.4 | 0.6 | 5 | Blue (BU) |
| 300-31277 | HIS-Pack-1/2 | 12.7 | 6.4 | 0.6 | 5 | Green-Yellow (GNYE) |
| 300-31900 | HIS-Pack-3/4 | 19.1 | 9.5 | 0.8 | 5 | Black (BK) |
| 300-31902 | HIS-Pack-3/4 | 19.1 | 9.5 | 0.8 | 5 | Red (RD) |
| 300-31903 | HIS-Pack-3/4 | 19.1 | 9.5 | 0.8 | 5 | Transparent (CL) |
| 300-31906 | HIS-Pack-3/4 | 19.1 | 9.5 | 0.8 | 5 | Blue (BU) |
| 300-31907 | HIS-Pack-3/4 | 19.1 | 9.5 | 0.8 | 5 | Green-Yellow (GNYE) |
| 300-32540 | HIS-Pack-1 | 25.4 | 12.7 | 0.9 | 5 | Black (BK) |
| 300-32542 | HIS-Pack-1 | 25.4 | 12.7 | 0.9 | 5 | Red (RD) |
| 300-32543 | HIS-Pack-1 | 25.4 | 12.7 | 0.9 | 5 | Transparent (CL) |
| 300-32546 | HIS-Pack-1 | 25.4 | 12.7 | 0.9 | 5 | Blue (BU) |
| 300-32547 | HIS-Pack-1 | 25.4 | 12.7 | 0.9 | 5 | Green-Yellow (GNYE) |

All dimensions in mm. Subject to technical changes.