

H365NR

Safety Switch , 400A, 600V, Fusible, Heavy Duty,
3-Pole



Technical Characteristics

Wire Size	#1/0 to 750 AWG/kcmil(Al/Cu)
Width	27.88 Inches
Depth	10.13 Inches
Height	50.31 Inches
Action	Single Throw
Ampere Rating	400A
Approvals	UL Listed
Catalog Reference Number	3100CT9801
Enclosure Type	Rainproof and Sleet/Ice proof (Indoor/Outdoor)
Electrical Interlock	None
Enclosure Rating	NEMA 3R
Enclosure Material	Galvannealed Steel
Factory Installed Neutral	Yes
Short Circuit Current Rating	10kA (Class H or K) - 200kA (Class R,J or L)
Maximum Voltage Rating	600V
Terminal Type	Lugs
Disconnect Type	Fusible
Mounting Type	Surface
Type of Duty	Heavy Duty
Number of Poles	3-Pole

Shipping and Ordering

Category	00054 - Safety Switch, Heavy Duty, NEMA3R, 400 - 1200 Amp, fused and unfused
Discount Schedule	DE1
Article Number	785901026686
Package Quantity	1
Weight	186 lbs.
Availability Code	Availability Code: D
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.