

## HIS-Service Station

This sturdy Service Station contains up to 5 dispensers. It can be put on a bench or mounted to a wall. A special cutter is included and makes it easy to cut the tubing length as desired

Technical Table	
Article-No.	Description
365-30100	<b>HIS-Service Station incl. cutter</b> , contents: 5 dispensers <b>HIS-3</b> (shrink ratio: 3:1), black, sizes are as follows: HIS-3/1, HIS-6/2, HIS-12/4 (2 pcs.), HIS-24/8
365-20000	<b>HIS-Service Station incl. cutter</b> , contents: 5 dispensers <b>HIS-Pack</b> (shrink ratio: 2:1), black, sizes are as follows: HIS-1/8, HIS-3/16, HIS-1/4, HIS-3/8, HIS 1/2 and one RiteOn Starter Pack
300-30000	<b>HIS-Service Station incl. cutter, empty</b>



HIS-Service Station contains 5 dispensers and a special cutter.

## HIS-Pack

### Features and Benefits

- E-beam Crosslinked Polyolefin, thin-wall and flexible
- Shrink ratio 2:1
- Available in colours: black, red, blue, transparent and yellow/green.
- 10 sizes from 1.2mm to 25.4mm
- Handy dispenser box including table with full range of applications

### Application

- General purpose electrical insulation
- Protection against corrosion and mechanical abrasion



HIS-A.

Material Data	
Material	<b>Polyolefin, Cross-linked (POX)</b>
Shrink Ratio	<b>2:1</b>
Longitudinal change after shrinkage	<b>-5% max.</b>
Minimum Shrink Temperature	<b>+120 °C</b>
Operating Temperature	<b>-55 °C to +135 °C</b>
Dielectric Strength	<b>25 kV/mm according to IEC 60684 P2</b>
Flammability	<b>ASTM D2671</b>



## HIS-Pack

Technical Table

Article-No.	Type	Supplied Ø D	Recov. Ø d	Wall (WT) nom.	Pack Cont. (m)	Colour
300-30120	HIS-Pack-3/64	1.2	0.6	0.4	10	Black (BK)
300-30122	HIS-Pack-3/64	1.2	0.6	0.4	10	Red (RD)
300-30123	HIS-Pack-3/64	1.2	0.6	0.4	10	Transparent (CL)
300-30126	HIS-Pack-3/64	1.2	0.6	0.4	10	Blue (BU)
300-30160	HIS-Pack-1/16	1.6	0.8	0.4	10	Black (BK)
300-30162	HIS-Pack-1/16	1.6	0.8	0.4	10	Red (RD)
300-30163	HIS-Pack-1/16	1.6	0.8	0.4	10	Transparent (CL)
300-30166	HIS-Pack-1/16	1.6	0.8	0.4	10	Blue (BU)
300-30240	HIS-Pack-3/32	2.4	1.2	0.5	10	Black (BK)
300-30242	HIS-Pack-3/32	2.4	1.2	0.5	10	Red (RD)
300-30243	HIS-Pack-3/32	2.4	1.2	0.5	10	Transparent (CL)
300-30246	HIS-Pack-3/32	2.4	1.2	0.5	10	Blue (BU)
300-30320	HIS-Pack-1/8	3.2	1.6	0.5	10	Black (BK)
300-30322	HIS-Pack-1/8	3.2	1.6	0.5	10	Red (RD)
300-30323	HIS-Pack-1/8	3.2	1.6	0.5	10	Transparent (CL)
300-30326	HIS-Pack-1/8	3.2	1.6	0.5	10	Blue (BU)
300-30327	HIS-Pack-1/8	3.2	1.6	0.5	10	Green-Yellow (GNYE)
300-30480	HIS-Pack-3/16	4.8	2.4	0.5	10	Black (BK)
300-30482	HIS-Pack-3/16	4.8	2.4	0.5	10	Red (RD)
300-30483	HIS-Pack-3/16	4.8	2.4	0.5	10	Transparent (CL)
300-30486	HIS-Pack-3/16	4.8	2.4	0.5	10	Blue (BU)
300-30487	HIS-Pack-3/16	4.8	2.4	0.5	10	Green-Yellow (GNYE)
300-30640	HIS-Pack-1/4	6.4	3.2	0.6	5	Black (BK)
300-30642	HIS-Pack-1/4	6.4	3.2	0.6	5	Red (RD)
300-30643	HIS-Pack-1/4	6.4	3.2	0.6	5	Transparent (CL)
300-30646	HIS-Pack-1/4	6.4	3.2	0.6	5	Blue (BU)
300-30647	HIS-Pack-1/4	6.4	3.2	0.6	5	Green-Yellow (GNYE)
300-30950	HIS-Pack-3/8	9.5	4.7	0.6	5	Black (BK)
300-30952	HIS-Pack-3/8	9.5	4.7	0.6	5	Red (RD)
300-30953	HIS-Pack-3/8	9.5	4.7	0.6	5	Transparent (CL)
300-30956	HIS-Pack-3/8	9.5	4.7	0.6	5	Blue (BU)
300-30957	HIS-Pack-3/8	9.5	4.7	0.6	5	Green-Yellow (GNYE)
300-31270	HIS-Pack-1/2	12.7	6.4	0.6	5	Black (BK)
300-31272	HIS-Pack-1/2	12.7	6.4	0.6	5	Red (RD)
300-31273	HIS-Pack-1/2	12.7	6.4	0.6	5	Transparent (CL)
300-31276	HIS-Pack-1/2	12.7	6.4	0.6	5	Blue (BU)
300-31277	HIS-Pack-1/2	12.7	6.4	0.6	5	Green-Yellow (GNYE)
300-31900	HIS-Pack-3/4	19.1	9.5	0.8	5	Black (BK)
300-31902	HIS-Pack-3/4	19.1	9.5	0.8	5	Red (RD)
300-31903	HIS-Pack-3/4	19.1	9.5	0.8	5	Transparent (CL)
300-31906	HIS-Pack-3/4	19.1	9.5	0.8	5	Blue (BU)
300-31907	HIS-Pack-3/4	19.1	9.5	0.8	5	Green-Yellow (GNYE)
300-32540	HIS-Pack-1	25.4	12.7	0.9	5	Black (BK)
300-32542	HIS-Pack-1	25.4	12.7	0.9	5	Red (RD)
300-32543	HIS-Pack-1	25.4	12.7	0.9	5	Transparent (CL)
300-32546	HIS-Pack-1	25.4	12.7	0.9	5	Blue (BU)
300-32547	HIS-Pack-1	25.4	12.7	0.9	5	Green-Yellow (GNYE)

All dimensions in mm. Subject to technical changes.