


PART NO.	BASE TYPE	DESIGN VOLTS	DESIGN AMPS	AVERAGE LIFE HOURS
LM1060MB	MINIATURE BAYONET	* 60 VAC	30mA	100,000

* OPERATIONAL VOLTAGE
54 - 66 VAC

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
1	ISSUED	1/21/2005	D.C.
2	OPERATIONAL VOLTAGE	06/23/2008	D.C.



COLOR	PART NUMBER	LUMEN
RED	LM1060MB-R	1.20
AMBER	LM1060MB-A	0.60
WHITE	LM1060MB-W	1.00
BLUE	LM1060MB-B	0.30
GREEN	LM1060MB-G	1.20
WARM WHITE	LM1060MB-WW	0.80

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES

DECIMALS ANGULAR
.XX ± .05 ± 0.5°
.XXX ± .010
FRACTIONAL ± 1/64

DRAWN D. C.	DATE 01/21/2005
CHECKED	
DESIGN	
MATERIAL	

CEC INDUSTRIES LTD

599 Bond Street

Lincolnshire IL 60069

TITLE

TRUE 360° LED MINIATURE BAYONET BASE LAMP
60 VOLT AC

SIZE A	FSCM NO.	DWG NO. LM1060MB	REV 2
SCALE	PLOT SCALE	SHEET 1 OF 1	
FILE LM1060MB.DWG	DO NOT SCALE DRAWING		