


PART NO.	BASE TYPE	DESIGN VOLTS	DESIGN AMPS	AVERAGE LIFE HOURS
LM1048MB	MINIATURE BAYONET	* 48 VAC	30mA	100,000

* OPERATIONAL VOLTAGE
43.2 - 52.8 VAC



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
1	ISSUED	1/21/2005	D.C.
2	OPERATIONAL VOLTAGE	06/23/2008	D.C.

COLOR	PART NUMBER	LUMEN
RED	LM1048MB-R	0.95
AMBER	LM1048MB-A	0.50
WHITE	LM1048MB-W	0.78
BLUE	LM1048MB-B	0.22
GREEN	LM1048MB-G	0.95
WARM WHITE	LM1048MB-WW	0.60

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES DECIMALS .XX ± .05 ANGULAR ± 0.5° .XXX ± .010 FRACTIONAL ± 1/64		CEC INDUSTRIES LTD	
		599 Bond Street	Lincolnshire IL 60069
DRAWN D. C.	DATE 01/21/2005	TITLE TRUE 360° LED MINIATURE BAYONET BASE LAMP 48 VOLT AC	
CHECKED		SIZE A	FSCM NO. DWG NO. LM1048MB REV 2
DESIGN		SCALE	PLOT SCALE SHEET 1 OF 1
MATERIAL		FILE LM1048MB.DWG	DO NOT SCALE DRAWING