


PART NO.	BASE TYPE	DESIGN VOLTS	DESIGN AMPS	AVERAGE LIFE HOURS
LM10160MB	MINIATURE BAYONET	160 VAC	30mA	100,000

OPERATIONAL VOLTAGE
144 - 176 VAC

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
1	ISSUED	1/21/2005	D.C.
2	OPERATIONAL VOLTAGE	06/23/2008	D.C.



COLOR	PART NUMBER	LUMEN
RED	LM10160MB-R	1.50
AMBER	LM10160MB-A	0.75
WHITE	LM10160MB-W	1.20
BLUE	LM10160MB-B	0.35
GREEN	LM10160MB-G	1.50
WARM WHITE	LM10160MB-WW	1.00

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES DECIMALS .XX ± .05 ANGULAR ± 0.5° .XXX ± .010 FRACTIONAL ± 1/64		CEC INDUSTRIES LTD			
		599 Bond Street Lincolnshire IL 60069			
DRAWN D. C.		DATE 01/21/2005		TITLE TRUE 360° LED MINIATURE BAYONET BASE LAMP 160 VOLT AC	
CHECKED		SIZE A		FSCM NO.	DWG NO. LM10160MB
DESIGN		SCALE		PLOT SCALE	SHEET 1 OF 1
MATERIAL		FILE LM10160MB.dwg		DO NOT SCALE DRAWING	
				REV 2	