

ECSP

Electronic Cleaning Solvent Plus

ECSP is an extremely fast-drying solvent specially formulated for the quick and efficient cleaning of electrical equipment. A version is available with integral brush for removing stubborn deposits.

- Non-halogenated cleaning solvent; will not attack the ozone layer
- Extremely fast evaporation rate; quick and efficient cleaning and degreasing
- Dries without leaving any residue; leaves a clean, dry surface in one cleaning step
- CO₂ propelled aerosol version available; 20% more active cleaner and can be used at 360° orientation

Approvals **RoHS-2 Compliant (2011/65/EU):** **Yes**

Typical Properties	Flash Point (°C)	-48
	Density @ 20°C (g/ml)	0.79
	Inhalation Toxicity (ppm)	500
	Residue on Evaporation (ppm)	<50
	Evaporation Rate	1.5 (ether = 1)

<u>Description</u>	<u>Packaging</u>	<u>Order Code</u>	<u>Shelf Life</u>
<u>Electronic Cleaning Solvent Plus</u>	200ml Aerosol	ECSP200D	36 Months
	200ml Aerosol with brush	ECSP200DB	48 Months
	400ml Aerosol	ECSP400D	36 Months
	6.25 Litre Bulk	ECSP6.25L	72 Months

Directions for Use

Suitable for a range of electrical contacts and components in electronic and video equipment, computers, optical and precision instruments, cameras, etc. Product contains flammable solvent so do not spray onto live electrical equipment or other sources of ignition. Immerse surface to be cleaned or spray onto surface to excess and allow to evaporate. A brush or foam tipped bud may be used to remove any stubborn deposits.

Revision 1: Oct 2013

Copyright Electrolube 2013

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification.

Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

Ashby Park, Coalfield Way,
Ashby de la Zouch,
Leicestershire LE65 1JR

T +44 (0)1530 419 600

F +44 (0)1530 416 640

BS EN ISO 9001:2008
Certificate No. FM 32082