



Tenma 72-10445

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
AC Current	40A/100A/400A/1000A	$\pm(2\%+5)$
AC Voltage	15V/100V/300V/600V	$\pm(1.2\%+5)$
Frequency	20Hz-500Hz	✓
Active Power	0.01KW-600KW	$\pm(3\%+5)$
Apparent Power	0.01KVA-600KVA	$\pm(4\%+5)$
Reactive Power	0.01KVA-600KVA	$\pm(4\%+5)$
Power Factor	0.3-1	$\pm(0.02\%+2)$
Phase Angle	0°-360°	$\pm 1^\circ$
Active Energy	1-9999KWh	$\pm(3\%+2)$
Special Functions		
Display Count		9999
Auto Range		✓
Jaw Capacity		50mm
True RMS	AC Voltage/AC Current	✓
Auto Power Off		✓
Low Battery Indication		✓
Data Hold		✓
Max/Min		✓
Data Logging		99
USB Interface		✓
LCD Backlight		✓
Full Icon Display		✓
Single-Phase 2-Wires		✓
3-Phase 3-Wires		✓
3-Phase 4-Wires		✓
Phase Sequence Test	Positive Phase,Reverse Phase,Phase Deficiency	✓
Auto Calibration		✓
Input Impedance for DCV	Around :10M Ω	✓

GENERAL CHARACTERISTICS

Power	1.5V Batteries (LR6) x 4	
LCD Size	46 x 42mm	
Product Colour	Orange and Grey	
Product Net Weight	601g	
Product Size	303 x 112 x 39mm	
Standard Accessories	Battery, Test Lead, Alligator Clip, USB Interface Cable, PC Software CD, Tool Box	
Standard Individual Packing	Gift Box ,English Manual	
Standard Quantity Per Carton	5pcs	
Standard Carton Measurement	480 x 372 x 315mm(0.056 CBM Per Standard Carton)	
Standard Carton Gross Weight	12kg	