

Part Number 3-689-15

Special pliers made from high grade special steel for extremely high requirements;
by precision inductiv hardness process blades achieve up to 65 HRC

Box joint

precise jaw adjustment without backlash

fine polished and bright burnished surface

Double leaf spring from stainless steel

Ergonomically formed bicoloured hand guard from dissipative anti-slide material

The pliers of this programm have been tested with good results by several test laboratories adequate to DIN EN 61340-5-1, DIN 61340-2-1, DIN 61340-2-3 for work in ESD protected areas.



Description: Flat nose pliers EUROline
extremely slim, long plain jaws,
angular

Characteristics:

Blade Finish -

Cutting capacity soft wire -

Cutting capacity medium wire -

cutting capacity hard wire -

A - Head width 12 mm

B - Head thickness 7,5 mm

C - Blade / jaw length 39 mm

Length 145 mm

Weight 100 g

Customs Tariff No. 82032000

EAN-No.

Link to catalogue page www.bernstein-werkzeuge.de/Katalogseiten/EUROline-Conductive_English.pdf

Link to image <http://www.bernstein-werkzeuge.de/Artikelbilder/03/3-689-15.jpg>

Image file 3-689-15.jpg

Keywords pliers; electronic pliers; flat nose pliers

