

Marine Products

20 Ampere, 125 Volt

2 Pole 3 Wire

TWIST-LOCK® Locking Type Devices



HBL23CM10



HBL7425WOA
HBL74CM25WOA



HBL23CM11



HBL60CM31



HBL23CM13



HBL60CM32



Plugs, receptacles and connectors only.

IP20

SUITABILITY Plugs and connectors only.



15A 125V

20A 125V Twist-Lock Devices

Description	Catalog Numbers
Yellow single receptacle has Rynite® body and abuse resistant nylon face.	HBL23CM10
Yellow polycarbonate spring-loaded lift cover plate for weatherproofing #HBL23CM10 receptacle. Meets the most stringent requirements of UL's three listing categories for weatherproof plates. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY.	HBL74CM25WOA
Same as #HBL74CM25WOA except gray in color. IP44 SUITABILITY.	HBL7425WOA
Yellow Insulgrip® plug has rugged nylon housing and cord grip with range of .325"-.930" (8-24) that utilizes a unique offset jaws arrangement to provide secure strain relief.	HBL23CM11
Yellow Seal-Tite® cover for weatherproofing #HBL26CM11 or #HBL23CM11 plugs. IP55 SUITABILITY. <i>Note: Fits Insulgrip® devices only.</i>	HBL60CM31
Yellow Insulgrip® connector body has rugged nylon housing and cord grip with range of .325"-.930" (8-24) that utilizes a unique offset jaws arrangement to provide secure strain relief.	HBL23CM13
Yellow Seal-Tite® cover for weatherproofing #HBL26CM13 or #HBL23CM13 connector bodies when used on extension cords or adapters. IP55 SUITABILITY. <i>Note: Fits Insulgrip® devices only.</i>	HBL60CM32
Yellow Valise® plug has one-piece nylon housing, assembles easily with two screws. Built-in cord grip has range of .460"-.720" (11.7-18.2).	HBL23CM11V
Yellow vinyl Seal-Tite® cover for weatherproofing #HBL23CM11V or #HBL26CM11V plugs. IP55 SUITABILITY. <i>Note: Fits Valise® devices only.</i>	HBL60CM31V
Three conductor, #12 AWG type STW, yellow PVC jacketed portable cord with jute fillers for added flexibility. Ideal for making cable sets, extension cords and adapters as will not mark boat's deck. Available in 250' (76.2m) lengths only.	YC312250*

*Not shown.

Rynite® is a registered trademark of E. I. DuPont.



HBL23CM11V





HBL60CM31V



Wiring Device-Kellems

www.hubbell-marine.com

Marine Products
20 Ampere, 125 Volt
 2 Pole 3 Wire
Straight Blade Devices



20A 125V Straight Blade Devices

Description	Catalog Numbers
Yellow Insulgrip® plug has rugged nylon housing and detachable cord grip with range of .230" to .720" (5.8-18.3) that utilizes unique offset jaws arrangement to provide secure strain relief.	HBL53CM66C
Yellow Insulgrip® connector body has rugged nylon housing and cord grip with range of .230"-.720" (5.8-18.3) that utilizes unique offset jaws arrangement for secure strain relief.	HBL53CM69C
Yellow Seal-Tite® cover for weatherproofing straight blade Insulgrip connector bodies, #HBL52CM69C and #HBL53CM69C, on extension cords and adapters. IP55 SUITABILITY. Not CSA. <i>Note: For Insulgrip® devices only.</i>	HBL60CM18
Yellow closure plug used with #HBL60CM18 long Seal-Tite cover to prevent water from entering front of device when not in use.	HBL60CM19
Yellow Seal-Tite® cover for weatherproofing straight blade Insulgrip plugs, #HBL52CM66C and #HBL53CM66C, when used to mate receptacles and connector bodies. Can also be used with Insulgrip connector bodies when mating with flanged inlets. IP55 SUITABILITY. Not CSA. <i>Note: For Insulgrip® devices only.</i>	HBL60CM17
Yellow duplex receptacle has Rynite® body. Receptacle accepts both 20A 125V and 15A 125V 2 pole, 3 wire straight blade plugs.	HBL53CM62
Single version of #HBL53CM62 duplex yellow receptacle .	HBL53CM61
Compact gray nylon panel mount outlet ideal for electric trolling motors and reel applications. Features gasketed spring-loaded lift cover for weatherproofing front and neoprene boot for weatherproofing rear. Accepts both 20A 125V and 15A 125V 2 pole, 3 wire straight blade plugs.	HBL61CM65
Same as #HBL52CM21 except for mounting to standard boxes. IP20 SUITABILITY. Not CSA.	HBL52CM22*
Same as #HBL52CM22 except gray in color. IP20 SUITABILITY. Not CSA.	HBL5222*
Yellow polycarbonate spring-loaded lift cover plate for weatherproofing duplex receptacles. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP20 SUITABILITY. Not CSA.	HBL52CM21
Same as #HBL52CM21 except gray in color. IP20 SUITABILITY. Not CSA.	HBL5221*
Yellow polycarbonate spring-loaded lift cover plate for weatherproofing single straight blade receptacles. Stainless steel screws and neoprene gasket included. For mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY. Not CSA.	HBL74CM23WO
Same as #HBL74CM23WO except gray in color. IP44 SUITABILITY. Not CSA.	HBL7423WO

*Not shown.

Rynite® is a registered trademark of E. I. DuPont.



HBL53CM66C



HBL53CM69C



HBL60CM18
HBL60CM19



HBL60CM17



HBL53CM62



HBL53CM61



HBL52CM21
HBL5221



HBL74CM23WO
HBL7423WO



HBL61CM65