

## WET & DRY VACUUM

NT 20/1 Ap 1.378-502.0 | NT 20/1 Ap Te 1.378-512.0

Kärcher NT 20/1 Ap (Te) is a powerful, compact and robust wet and dry vacuum cleaner. The compact and robust design of the machine is especially suitable for operators who often change their location. It provides high stability while maintaining high suction power, thanks to the semi-automatic filter cleaning system.



### Technical Specification

Wet & Dry Vacuum	NT 20/1
Air flow rate (l/s)	74
Maximum motor rating (W)	1350
Container capacity (l)	20
Noise level (dB)	66



#### Constant suction power with the Ap function

- The semi-automatic filter cleaning system (Ap = all purpose) ensures constant suction power and therefore fewer working interruptions.



#### Excellent mobility and stability

- The compactness (square design) and the ergonomically formed handle the machine is easy to transport and convenient to store in a van, car, etc



#### On-board accessory and cable storage

- Accessories and small parts can be stored safely on the vacuum head and are therefore always be available to hand quickly for all your cleaning applications.



#### (Te) Power tool auto start

- The a power tool take-off socket with automatic power tool on/off function which enables the vacuum to be switched on and off through the power tool - saving energy, reducing noise, and ensuring that dust made by power tools goes straight into the container.

makes a difference

## Vacuum Cleaner Accessories

Maximising the potential of your Kärcher machine



### Filter Bags

Three different filter bag types available: paper bags for dust class M, tear-resistant fleece bags and fabric bags which can be washed and re-used.



### Gangway Tool

Enables large hard floor areas to be cleaned quickly and efficiently. Rubber lips and brush strips supplied as standard for wet or dry pick-up.



### Nozzle Set

Consisting of crevice tool, upholstery tool, suction brush and storage clip, this kit keeps essential nozzles tidy and close-by.



### Detail Brush

A suction brush designed for cleaning smaller, hard to reach areas. With plastic or natural bristles to suit the surface being cleaned.



### Rubber Suction Tool

This soft rubber tool is ideal for thorough, damage-free cleaning of sensitive surfaces.



### Pipe Dusting Nozzle

Designed exclusively for fast and effective cleaning of pipe work which can be difficult to clean with normal tools. Two sizes available to suit different pipe diameters.



### Radiator Brush

Designed for easy cleaning behind radiators and other narrow spaces. For use with a crevice tool.



### Upholstery Nozzle

For easy, thorough cleaning of upholstery, curtains and car seats.



### Filters

HEPA filters, PES filters and exhaust filters are designed to suit specific applications and the dust type being vacuumed.



### Repair Kits

Suction hose repair kits can mend damaged or split hoses quickly, saving time and money. Suitable for a wide range of suction hoses.



### Suction Hoses

A wide range of hoses to suit different applications, from basic extension hoses to electrically-conductive or oil resistant hoses, in lengths from 2.5m to 10m. Kärcher's clip system makes the changing of hoses fast and simple.



### Couplings

A wide range available, including connecting sleeves to connect more than one suction hose together and V-piece adapters for using two suction hoses at once.



### Bends

A range of bends in metal, stainless steel and plastic, including an electrically-conductive version to reduce electrostatic charging.



### Suction Tubes

A range of tubes in metal, stainless steel and plastic, including a telescopic version with adjustable length from 0.6m to 1m.



### Accessory Kits

Versatile accessory kits designed for specific trades and applications including plumbing, building and vehicle valeting. The power tool kit is designed to work with Te machines when using equipment such as electric sanders.



### All-Purpose Tool

All tools available from 300mm to 450mm for fast and effective cleaning of hard floors. Rubber lips and brush strips supplied as standard for wet or dry pick-up.



### Car Cleaning Nozzle

A 90mm wide plastic nozzle designed specifically for fast, thorough cleaning of car, van and truck interiors. Effective in hard to clean areas such as under seats, upholstery seams and storage areas.



### All-Purpose Brush

Natural bristles provide excellent cleaning results for any hard surface. Versions available to fit all models in the Kärcher range.

### Other machines in the range



45 Litre Wet & Dry Vacuum Cleaner



65 Litre Wet & Dry Vacuum Cleaner



10 Litre Energy Saving Dry Vacuum Cleaner



Spray Extraction Carpet Cleaner



5 Litre Battery Powered Sweeper



Compact Cold Water Pressure Washer

### You might also consider

Tel: + 44 01295 752 082

Kärcher (UK) Ltd  
Beaumont Road  
Banbury, Oxon OX16 1TB  
info@karcher.co.uk  
www.karcher.co.uk

Tel: +353 (0) 1 409 7777

Kärcher Ltd. (Ireland)  
Unit 4 EP Mooney Business Park  
Walkinstown Avenue, Dublin 12  
info@ie.karcher.com  
www.karcher.ie