This document was generated on 12/11/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0022013137
Status: Active
Overview: KK® Interconnect System - Molex
Description: KK® 254 Crimp Housing, Friction Ramp, 13 Circuits

Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Product Specification PS-10-07 (PDF)
Packaging Specification PK-2695-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	2695
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	800753593473
Physical	
Circuits (maximum)	13
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.381/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	See Product Specification
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Old Part Number	2695-13RP
Reference - Drawing Numbers	
Packaging Specification	PK-2695-001
Product Specification	PS-10-07
Sales Drawing	SD-2695

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
No -ED/39/2015 (15 June 2015)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series
2695 Series

Mates With
KK®254 PCB Headers 42375 , 42377 , 42376 , 4030 , 6373 , 6410

Use With
2759 , 4809 KK® Crimp terminal

This document was generated on 12/11/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION