

SDRW-08D2S-U



Color

Black
White

Read Speed

DVD+R : 8X
DVD-R : 8X
DVD+RW : 8X
DVD-RW : 8X
DVD-ROM : 8X
DVD+R(DL) : 8X
DVD-R(DL) : 8X
DVD-ROM(DL) : 8X
DVD-RAM : 5X
CD-R : 24X
CD-RW : 24X
CD-ROM : 24X
DVD Video Playback : 4X
VCD Playback : 10X
Audio CD Playback : 10X

Write Speed

DVD+R : 8X
DVD-R : 8X
DVD+RW : 8X
DVD-RW : 6X
DVD+R(DL) : 6X
DVD-R (DL) : 6X
DVD-RAM : 5X
CD-R : 24X
CD-RW : 16X

Writing Mode	DVD+R & DVD+R (DL) : Sequential Write DVD-R & DVD-R(DL) : DAO/Incremental Recording DVD+RW : Random Write DVD-RW : DAO/Restricted Overwrite/Incremental Recording DVD-RAM : Random Write CD-R/RW : DAO/TAO/SAO/Packet Write
Access time	DVD : 160 ms CD : 140 ms
Interface	USB 2.0
OS Support	Windows® 8 Windows® 7 Windows® Vista Windows® XP Windows® Server 2003 Windows® Server 2008 Mac OS X 10.5
System Requirements	CPU: Intel Pentium® 4 2.0GHz or AMD Athlon 2100+ or higher RAM: 512 MB or more is recommended HDD: 10 GB or higher
Software	Cyberlink Power2Go 7 E-Green

Disc Formats	Audio CD, Video CD, CD-I, CD-Extra, Photo CD, CD-Text, CD-ROM/XA, Multi-session CD, CD-R, CD-RW, CD-ROM , DVD±R(SL/DL), DVD±RW, DVD-ROM(SL/DL), DVD-RAM, DVD Video
Disc Diameters	12cm/8cm
Mounting Orientation	Vertical and Horizontal (+5° ~ -5°)
Dimensions	142 x 142 x 20 mm (LxWxH)
Weight	280 g
Power	USB Power +5V ± 5%
Temperature	Operating : 5 °C to 40 °C Storage : -30 °C to 60 °C
Humidity	Operating : 15 % ~ 80 % (Non-condensing) Storage : 10 % ~ 90 % (Non-condensing)