

**BOSCH**

Invented for life

Power tools for trade & industry

Product data sheet



Cordless Torch

GLI VariLED

The brightest pocket-sized worklight

The most important data

Battery voltage	14,4–18 V
Operating time	150–420 mins
Weight (without battery)	0,3 kg

Part number: 0 601 443 400**GBP 55,00***[> More product information](#)** Recommended retail price excluding VAT*

Technical data


Operating time	150–420 mins
Weight (without battery)	0,3 kg
Length	130,0 mm
Width	80,0 mm
Height	40,0 mm
Battery voltage	14,4–18 V
Brightness	300 lx
Operating time (18 V / 3.0 Ah)	420 mins
Operating time (14.4 V / 3.0 Ah)	330 mins
Operating time 14.4 V	115 mins/Ah
Operating time 18 V	135 mins/Ah

**BOSCH**

Invented for life

Power tools for trade & industry**Advantages:**

- Brightest light (300 lux) in its class due to 3 innovative Power LEDs
- Very compact due to innovative folding mechanism
- Versatile range of applications due to adjustable light beam (spot/flood) and 9 settable lighting angles
- For flexible use with all Bosch 14.4 and 18 volt lithium-ion batteries
- Extremely robust: fully functional, even after falling 2 m onto concrete, due to tough housing
- Practical hard rubber strap for fixing the worklight to enable targeted illumination of the work area

**Prices / Scope of delivery**

Part number	0 601 443 400
Battery and charger not included	✓
Belt clip	✓
Solo Version	✓
Price (Recommended retail price excluding VAT)	GBP 55,00