This document was generated on 10/30/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0039000217
Status: Active
Overview: Mini-Fit Jr.™ Power Connectors
Description: Mini-Fit® Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 16 AWG, Reel

Series image - Reference only

Documents:

Drawing (PDF)
Product Specification PS-5556-001 (PDF)
Product Specification PS-5556-002 (PDF)
Packaging Specification PK-5556-001 (PDF)
Test Summary TS-5556-002 (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit®
UPC	800755527940
Physical	
Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.133/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	9.0A
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Old Part Number	5556-PBS3P
Reference - Drawing Numbers	
Packaging Specification	PK-5556-001
Product Specification	PS-5556-001, PS-5556-002
Sales Drawing	SD-5556-SP*
Test Summary	TS-5556-002

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Contains SVHC(2015 June 15): No

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series
5556 Series

Mates With
5558 Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, 5566 , 5569

Use With
5557 Mini-Fit Jr.™ Receptacle Housing, 30067 Mini-Fit® TPA, 42474 Mini-Fit® BMI Panel Mount, 5559 Mini-Fit Jr.™ Plug Housing, Dual Row

Application Tooling | **FAQ**

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	**Product #**

FineAdjust™ Applicator for Mini-Fit Jr.™, Mini-Fit HCS™, and Mini-Fit Plus HCS™ Crimp Terminals, 16 AWG with Large Insulation Diameters	0639041400
T2 Terminator™ for insulation OD 2.60-3.15mm optimized for 16 AWG only	0639102800
T2 Terminator™ for insulation OD 2.20-2.45mm optimized for 16 AWG only	0639103000
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	0638190900
Extraction Tool	0011030044
FineAdjust™ Applicator for Insulation OD 2.20-2.45mm, Optimized for 16 AWG Only	0639039400
FineAdjust™ Applicator for Insulation OD 1.80-2.20mm Optimized for 16 AWG Only	0639015300