

Product information

12V 10MM DRILL DRIVER



6271DWPE

Voltage	12 v
Max Size Wood Screw	12 mm
No Load Speed	H: 0 - 1300 / L: 0 - 400 rpm
Torque Settings; S/H Nm	16; 18/30
Battery Type	Ni-Cad
Charging Time	30 min
Battery Quantity (1.3Ah)	2
Vibration: Drilling	2.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)
Net weight	1.5 kg



- Compact & Lightweight
- Ideal for working in confined space
- Keyless Chuck
- Variable speed
- Reversible

Details correct as of: 21-12-2015

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com