3M™ Field Service Kit 8507



[click to enlarge]

GTIN(UPC/EAN): 0 00 51138 55387 6

3M Id: 98-0798-3093-5

3M™ Portable Field Service Kit 8507 (Premium Performance) - The 3M Portable Field Service Kit 8507 with a 3M™ Wrist Strap Monitor 725 bundles together two static control products to give a field technician the same continuously monitored, static protected working environment as that enjoyed by workers in a manufacturing facility.

Kit contains:

Static Dissipative Worksurface, foldable, $0.021 \text{ H} \times 22 \text{ W} \times 24 \text{ in. L}$ (0.53 mm x 56 cm x 61 cm) red with gray cotton edging. Two pockets, each 8 in. x 11 in. (20.3 cm x 28.0 cm), ground snap.

 $3M^{\text{TM}}$ Wrist Strap Monitor 725, 2.5 H x 2.6 W x 1.1 in. L (6.4 x 6.6 x 2.8 cm), black. Battery-powered, 9 V (not included). Ground cord, 6 ft. (1.8 m), with ground clip. Ground snap on unit to connect to the worksurface.

3M™ Dual Conductor Adjustable Fabric Wrist Band 2368

3M[™] Dual Conductor Coiled Cord 2370, 10 ft. (3.0 m)

Characteristics

Color	Red
Dissipative	Yes
Kit Type	Portable
Length	24 Inch
Primary Trademark Name	3M
Thickness	0.021 Inch
Width	22 Inch