
1-800-383-7323 USA/CAN www.energizer.com

EVEREADY 412



Industry Standard Dimensions

mm (inches)



Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

Designation: ANSI / NEDA-215, IEC-15F20

Battery Voltage: 22.5 Volts

Average Weight: 38 grams (1.3 oz.)

Volume: 21 cubic centimeters (1.3 cubic inch)


Average Capacity: 140 mAh to 0.8 volts/cell

(Rated at 25 mA continuous drain at 21°C)

Cells: Fifteen No. 112 in series

Jacket: Metal

TYPICAL DISCHARGE CURVE



Simulated Application Test Estimated Average Service at 21°C (70°F)

| | Typical Drains at 18V | Load | Cutoff Voltage |
|-------------|--------------------------|--------|-------------------------------|
| Schedule: | (milliamperes) | (ohms) | 12V 13.5V 15V 16.5V 18V 19.5V |
| | | | Hours |
| 4 hours/day | 0.8 | 22,500 | 209 197 184 167 134 55 |

Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. Inc. - All Rights Reserved

Form No. EBC - 3219D Page 1 of 1