

PICCOLO ABS D 85 G



Sample photo

Order symbol: ABS D 85 G
Product nbr: 8784308
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074002174
El. number:
Finland: 3423461
Electric No. Denmark: 8212001912
Electric No. Italy: 7211035
Electric No. Sweden: 2536717

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:			Accessories:		
mm:	170	80	85	DH-3	DIN-35 Mounting rail
inch:	6.7	3.1	3.3	FP 22040	Wall fastening lug (2 pcs)
Materials:			Rating:		
Material:	ABS		Ingress Protection (EN 60529): IP66/IP67		
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK07		
Cover screws material:	Polyamide		Electrical insulation: Totally insulated		
Cover colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1		
Cover screws colour:	Grey		Flammability Rating: UL 94 HB		
Gasket material:	Polyurethane		Glow Wire Test (IEC 695-2-1) °C: 650		
			NEMA Class: NEMA 1, 4, 4X, 6, 6P, 12, 13		
Temperatures:					
Temperature °C (short term):	-40 ... 80 °C				
Temperature °C (continuous):	-40 ... 60 °C				
Temperature °F (short term):	-40 ... 175 °F				
Temperature °F (continuous):	-40 ... 140 °F				
Accessories:					
D-MP	Mounting plate				

PICCOLO 170x80x65-85

