



Sample photo

Order symbol: PCM 200/63 G
Product nbr: 6016324
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074051950
El. number:
Finland: 3435270
Electric No. 8212027446
Denmark:
Electric No. Sweden: 2535342

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:		
mm:	255	180	63	MIN 15	DIN-15 Mounting rail
inch:	10.0	7.1	2.5	MIN 20	DIN-15 Mounting rail
			MIV 15	DIN-35 Mounting rail	
			MIV 20	DIN-35 Mounting rail	
			FP A 200/180	Front plate (Aluminium)	
			HFP 180	Front plate hinge series	
			FP 22046	Wall fastening lug (4 pcs)	
Materials:			Rating:		
Material:	Polycarbonate		Ingress Protection (EN 60529): IP66/IP67		
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK08		
Cover screws material:	Polyamide		Electrical insulation: Totally insulated		
Cover colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1		
Cover screws colour:	Grey		UV resistance: UL 508		
Gasket material:	TPE		Flammability Rating: UL 746C 5V		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13		
Temperatures:			Certificates:		
Temperature °C (short term):	-40 ... 120 °C		Germanischer Lloyd (GL)		
Temperature °C (continuous):	-40 ... 80 °C		SGS Fimko		
Temperature °F (short term):	-40 ... 250 °F		Gost R		
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
MIV 200	Mounting plate (Galvanized steel)				

