



Sample photo

Order symbol: PC 233011
Product nbr: 7032890
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074003713
EI. number:
 Finland: 3423446
 Electric No. Denmark: 8212003046
 Electric No. Italy: 7301065
 Electric No. Sweden: 2536137

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	300	230	110	Ingress Protection (EN 60529): IP66/IP67
inch:	11.8	9.1	4.3	Impact Resistance (EN 62262): IK07/IK08
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			UV resistance: UL 508
Cover screws material:	Stainless steel			Flammability Rating: UL 746C 5V
Cover colour:	RAL 7035 -light grey			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:				Certificates:
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C			Gost R
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

EURONORD PC/ABS 300x230x87-110

