

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010011034](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: 5.08mm Pitch KK® Crimp Terminal Housing, 3 Circuits

Documents:
[3D Model](#) [Product Specification PS-99020-0087 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	3001
Application	Power, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK®
UPC	800753613065
Physical	
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	0.925/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm
Temperature Range - Operating	See Product Specification
Solder Process Data	
Lead-freeProcess Capability	WAVE
Material Info	
Old Part Number	3001-03
Reference - Drawing Numbers	
Product Specification	PS-99020-0087
Sales Drawing	SDE-3001-N-*



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC No -ED/39/2015 (15 June 2015) Halogen-Free Status Low-Halogen	China RoHS
--	-------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series
[3001](#) Series

Mates With
[3061](#) , [3003](#) , [3008](#)

Use With
[2478](#) Crimp Terminals for 18-24 AWG, [2578](#) Crimp Terminals for 22-26 AWG, [2878](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION