





DESCRIPTION: M5 FEMALE - CABLE MOUNT - SOLDER CUP - 4 POSITION



NUT



NOTE:

MATERIAL

HOUSING: TPU, BLACK  
CONTACT: PHOSPHOR BRONZE  
NUT: BRASS  
O-RING: NBR, BLACK

FINISH

CONTACT: GOLD FLASH (0.8-1.0) $\mu$   
OVER 50 $\mu$  NICKEL  
SATIN NICKEL

NUT:


ELECTRICAL

RATED CURRENT: 1A  
RATED VOLTAGE: 60V  
WATER PROOF: IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C

WIRE GAUGE: 26-28 AWG



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

08/17/14

CHECKED:

DATE:

NorComp

SCALE:

NTS

SHEET

OF

1 1

REV

0

DWG NO.

850-004-203RLU1