





DESCRIPTION: M5 MALE - RIGHT ANGLE - 4 POSITION

NOTE:


MATERIAL	
HOUSING:	PBT UL94V-0, BLACK
CONTACT:	BRASS
NUT:	BRASS
O-RING:	NBR, BLACK
BACK HOUSING:	PBT UL94V-0, BLACK
DOWN HOUSING:	PBT UL94V-0, BLACK
FINISH	
CONTACT:	GOLD FLASH OVER ALL
UNDER PLATE:	NICKEL
SHELL:	STAIN NICKEL
	80µ" OVER ALL
ELECTRICAL:	
RATED CURRENT:	1A
RATED VOLTAGE:	60V
WATER PROOF:	IP67
ENVIRONMENT:	
OPERATION TEMPERATURE:	
-40°C TO +85°C	



NUT



P.C.B LAYOUT



PANEL CUT-OUT

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH
CHECKED:

DATE: 08/17/14
DATE:

NorComp

SCALE: NTS	SHEET 1 OF 1	REV 0
DWG NO. 853-004-113R001		