

NOTE:

MATERIAL

HOUSING: PBT UL94V-0, BLACK  
 CONTACT: BRASS  
 NUT: BRASS  
 O-RING: NBR, BLACK  
 BACK HOUSING: PBT UL94V-0, BLACK  
 DOWN HOUSING: PBT UL94V-0, BLACK

FINISH




CONTACT: GOLD FLASH OVER ALL  
 UNDER PLATE: NICKEL  
 NUT: STAIN NICKEL

ELECTRICAL:


RATED CURRENT: 1A  
 RATED VOLTAGE: 60V  
 WATER PROOF: IP67

ENVIRONMENT:


OPERATION TEMPERATURE: -40°C TO +85°C



NUT



P.C.B LAYOUT



PANEL CUT-OUT

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH

DATE: 12-05-14

CHECKED:

DATE:

NorComp

SCALE: NTS

SHEET 1 OF 1

REV 0

DWG NO.

853-004-213R001