




DESCRIPTION: M8 MALE - CABLE MOUNT - SOLDER CUP - 4 POS.



NOTE:

MATERIAL

HOUSING: PBT UL94V-0, BLACK
CONTACT: COPPER ALLOY
NUT: COPPER ALLOY
SHELL: COPPER ALLOY
O-RING: NBR, BLACK

FINISH



CONTACT: GOLD FLASH 10µ MIN.
OVER 50µ NICKEL
NUT: NICKEL PLATED 60-100µ OVER ALL
SHELL: NICKEL PLATED 60-100µ OVER ALL

ELECTRICAL

RATED CURRENT: 5A
RATED VOLTAGE: 125V
WATER PROOF: IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C
WIRE GAUGE: 24-28 AWG



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH
CHECKED:

DATE: 08-14-14
DATE:

NorComp

SCALE: N.T.S.
SHEET 1 OF 1
REV 0
DWG NO. 854-004-103RLS4