

DESCRIPTION: M8 FEMALE - CABLE MOUNT - SOLDER CUP - 5 POS.

UNITS = INCHES [MM]

NOTE:

MATERIAL


HOUSING: PBT UL94V-0, BLACK
CONTACT: BRASS
NUT: BRASS
GROUND: BRASS
O-RING: NBR, BLACK
FINISH
CONTACT: GOLD FLASH
OVER 50µ" NICKEL
NUT: NICKEL PLATED
GROUND: BRIGHT TIN (60µ")

ELECTRICAL





RATED CURRENT: 3A
RATED VOLTAGE: 125V
WATER PROOF: IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C
WIRE GAUGE: 24-28 AWG



NUT



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON
CHECKED:

DATE: 03-17-15
DATE:

NorComp

SCALE: N.T.S.

SHEET 1 OF 1

REV 0

DWG NO.

WP-05F2-92-11