



DESCRIPTION: M12 MALE - PANEL MOUNT (REAR) - SOLDER CUP - 12 POS.



PANEL CUTOUT

PCB LAYOUT



NUT

NOTE:

MATERIAL

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

BRASS

NUT:

BRASS

O-RING:

EDPM

FINISH

CONTACT:

GOLD 10µ" MIN.

OVER 50µ" NICKEL

NICKEL PLATED

NUT:

ELECTRICAL

RATED CURRENT:

1A

RATED VOLTAGE:




30V

WATER PROOF:

IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

01-16-15

CHECKED:

DATE:

NorComp

SCALE:

N.T.S.

SHEET

OF

1

1

REV

0

DWG NO.

860-012-113R004