

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009508033

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 3 Circuits

Documents:

3D Model

Packaging Specification PK-41695-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-08-50 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

41695

Application

Power, Wire-to-Board

MolexKits

Yes

Overview

KK® Interconnect System - Molex

Product Name

KK® 396

UPC

800753613799

Physical

Breakaway

No

Circuits (maximum)

3

Color - Resin

Natural

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Resin

Polyester

Net Weight

1.095/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.96mm

Polarized to Mating Part

Yes

Temperature Range - Operating

See Product Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Old Part Number

41695-N-D3

Reference - Drawing Numbers

Packaging Specification

PK-41695-001

Product Specification

PS-08-50

Sales Drawing

SD-41695



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

No -ED/39/2015 (15 June 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

41695 Series

Mates With

KK® 396 Header [41791](#) , [41792](#) , [41671](#) , [41672](#) , [41661](#) , [41662](#)

Use With

KK® 396 Crimp Terminals, [2478](#) , [2578](#) , [6838](#) , [7258](#) , [45570](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION