



15" 1600W Bluetooth Music Streaming Portable Loudspeaker System

Model: PPHP159WMU

Technical Specs:



- Max Power Output: 1600w
- RMS Power Output: 800w
- Battery Life: Up to 4 Hrs
- Battery Charge Time: Approx. 8 Hrs
- Subwoofer Frequency: 75-18kHz
- Subwoofer: 15"
- Tweeter: 1.3"
- Impedance: 4 Ohm
- Sensitivity: 96dB (+/-2dB)
- S/N Ratio: >50dB
- T.H.D.: 0.3%, 25 Watt
- Frequency Response: 55-18kHz
- Power: 110-220v Switchable
- Maximum USB/SD Card Support: 16GB
- Digital Audio File Support: .mp3, .wma, .avi
- Dimensions (LxWxH): 17.3"x14.6"x26.8"

Contents: PA Speaker, (2) wireless handheld microphones, attachable mic holders, attachable rolling wheels, remote control, power/charging cable.

Sold as: Unit

Weight: 51lbs

Pyle has been in business for over 35 years, and their manufacturing experience and expertise is easy to see – and hear. Pyle drivers are all manufactured with close attention to detail, and maintain tight manufacturing tolerances, which are both necessary to produce a quality product. The Pyle PPHP159WMU Bluetooth PA speaker is a wide-coverage, two-way loudspeaker system that covers the complete audio spectrum. Built-in Bluetooth wireless streaming technology allows you to pair it with your favourite devices to enable powerful full-range distortion-free sound.