






THIS DRAWING IS A CONTROLLED DOCUMENT. DRAW NO 1583004

TOOL NUMBER	WIRE SIZE mm ² [AWG]	INSULATION DIAMETER mm [in.]	INSUL. ADJ.	FLIP LOCATOR	STRIP LENGTH mm [in.]	CRIMP HEIGHT mm [in.]	CONTACT PART NUMBERS 						CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.		
							LOOSE PIECE			STRIP FORM						
91505-1	0.2 - 0.6 [24-20]	1.14 - 1.78 [.045-.070]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.01 ± 0.05 [.039 ± .002]	66103-[] 66400-[] 164163-[]	66105-[] 163086-[]	66399-[] 163088-[] 170246-[] 170248-[] 66702-[]	66102-[] 66332-[] 164160-[]	66104-[] 163085-[]	66331-[] 163087-[] 170245-[] 170247-[]	Type III+ (yellow)	114-10004		
91505-3	0.8 - 1.4 [18-16]	2.03 - 2.54 [.080-.100]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.30 ± 0.05 [.051 ± .002]	66099-[] 164164-[] 66589-[]	66101-[] 163082-[] 164839-[] 170244-[] 66590-[]	163084-[] 164840-[] 170242-[]	66098-[] 164161-[] 66579-[]	66100-[] 163081-[] 163766-[] 170243-[] 66580-[]	163083-[] 163767-[] 170241-[]	Type III+ (blue and violet)	114-10004		
91515-1	0.05 - 0.38 [30-22]	1.02-1.91 [.040-.075]	NO	NO	3.50-4.75 [.140-.187]	0.79 ± 0.05 [.031 ± .002]	61173-[]	61174-[]	350078-[]	350079-[]	COMMERCIAL M-N-L		114-1012			
91515-3	0.08 - 0.24 [28-24]	0.89-1.40 [.035-.055]					66107-[] 163092-[] 66595-[]	66109-[] 164163-[] 66596-[]	163090-[] 170250-[] 170252-[]	66106-[] 163091-[] 66585-[]	66108-[] 164160-[] 66586-[]	163089-[] 170249-[] 170251-[]	Type III+ (red)	Type VI	114-10004	114-10007
91515-3	0.2 - 0.6 [24-20] 0.05 - 0.15 [30-26]	1.14-1.78 [.045-.070]					66103-[] 163088-[] 66428-[] 66593-[]	66105-[] 164162-[] 66429-[] 66594-[]	163086-[] 170246-[] 170248-[]	66102-[] 163087-[] 66424-[] 66583-[]	66104-[] 164159-[] 66425-[] 66584-[]	163085-[] 170245-[] 170247-[]	Type III+ (yellow & brown)	Type VI	114-10004	114-10007
91519-1	0.8 - 1.4 [18-16]	2.03-2.54 [.080-.100]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.30 ± 0.05 [.051 ± .002]	66360-[] 66361-[]			66358-[] 66359-[]		Type III+	114-10004			
91519-3	1.9 - 2.1 [14]						1.73 ± 0.05 [.068 ± .002]	66601-[] 66602-[]		66598-[] 66597-[]		213603-1 213603-3		Type III+	114-10004	
91521-1	0.8 - 1.4 [18-16]	2.79-3.81 [.110-.150]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.30 ± 0.05 [.051 ± .002]	213603-2 213603-4			66332-[] 66331-[]		Type III+ (yellow)	114-10004			
91521-3	1.9 - 2.1 [14]						1.73 ± 0.05 [.068 ± .002]	66400-[] 66399-[]			66332-[] 66331-[]		Type III+ (yellow)	114-10004		
91523-1	0.2 - 0.6 [24-20]	2.03-2.54 [.080-.100]	NO	NO	3.56-4.75 [.140-.187]	0.99 ± 0.05 [.039 ± .002]	163082-[] 164164-[] 66101-[]			163081-[]	164161-[]	66100-[]	Type III+ (blue)	114-10004		
91523-3	0.8 - 1.4 [18-16]						1.30 ± 0.05 [.051 ± .002]	163084-[] 66099-[] 170242-[]			163083-[]	66098-[]	170241-[]	170243-[]	66579-[]	66580-[]
91542-1	0.2 - 0.35 [24-22]	1.52-3.43 [.060-.135]	YES	NO	3.96 ± 0.38 [.156 ± .015]	0.89 ± 0.08 [.035 ± .003]	66565-[]			66563-[]		Type III+ (yellow)	114-10004			
91542-3	2X 0.2 DR 0.56 [2X 24 DR 20]						0.99 ± 0.08 [.039 ± .003]	66566-[]			66564-[]		Type III+ (yellow)	114-10004		
91550-1	0.8 - 1.4 [18-16]	2.03-3.43 [.080-.135]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.30 ± 0.05 [.051 ± .002]	66587-[]			66577-[]		Type VI	114-10007			
91550-3	1.9 - 2.1 [14]						1.73 ± 0.05 [.068 ± .002]	66588-[]			66578-[]		Type VI	114-10007		





 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

- 2. AMP and CERTI-CRIMP are trademarks.
-  -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
- 4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET



DWN: M. YOUNGER 21FEB2012		MATERIAL: -		HEAT TREAT: -																												
CHK: B.A. WOLFE 22FEB2012		APVD: B.A. WOLFE 22FEB2012		 TE Connectivity																												
NAME: B.A. WOLFE		DRAWING NO: 1583004																														
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SCALE: -																												
<table border="1" style="font-size: small;"> <tr><td>0</td><td>PLC</td><td>± .-</td></tr> <tr><td>1</td><td>PLC</td><td>± .-</td></tr> <tr><td>2</td><td>PLC</td><td>± .-</td></tr> <tr><td>3</td><td>PLC</td><td>± .-</td></tr> <tr><td>4</td><td>PLC</td><td>± .-</td></tr> </table>		0	PLC	± .-	1	PLC	± .-	2	PLC	± .-	3	PLC	± .-	4	PLC	± .-	<table border="1" style="font-size: small;"> <tr><td>AW</td><td>BAW</td></tr> <tr><td>DATE</td><td>09/2015</td></tr> <tr><td>REVISION RECORD</td><td></td></tr> </table>		AW	BAW	DATE	09/2015	REVISION RECORD		<table border="1" style="font-size: small;"> <tr><td>SIZE</td><td>A1</td></tr> <tr><td>REV</td><td>1 of 2</td></tr> <tr><td>SHEET</td><td>D</td></tr> </table>		SIZE	A1	REV	1 of 2	SHEET	D
0	PLC	± .-																														
1	PLC	± .-																														
2	PLC	± .-																														
3	PLC	± .-																														
4	PLC	± .-																														
AW	BAW																															
DATE	09/2015																															
REVISION RECORD																																
SIZE	A1																															
REV	1 of 2																															
SHEET	D																															
SURFACE TEXTURE: 		ANGLES: -		DRAWING NO: 1583004																												

LOC A
DIST 00

TOOL NUMBER	WIRE SIZE mm ² [AWG]	INSULATION DIAMETER mm [in.]	INSUL. ADJ.	FLIP LOCATOR	STRIP LENGTH mm [in.]	CRIMP HEIGHT mm [in.]	CONTACT PART NUMBERS ¹						CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
							LOOSE PIECE			STRIP FORM				
 -1 -3 ³														
91564-1 91564-3	0.20-0.56 [24-20]	1.02-2.03 [.040-.080]	NO	NO	3.55-4.75 [.140-.187]	1.00 ± 0.05 [.039 ± .002]	66103-[]	66593-[]	66596-[]	66102-[]	66583-[]	66586-[]	Type III+ (yellow) (red)	114-10004
	0.05-0.15 [30-26]	1.02-1.52 [.040-.060]					66105-[]	170246-[]	66594-[]	66104-[]	170245-[]	66584-[]		
	0.12-0.22 [26-24]	0.89-1.40 [.035-.055]					66429-[]	170248-[]		66425-[]	170247-[]			
						0.79 ± 0.04 [.031 ± .002]	66107-[]	66237-[]	170252-[]	66106-[]	170249-[]			
							66109-[]	170250-[]		66108-[]	170251-[]			

- ¹ LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.
2. AMP and CERTI-CRIMP are trademarks.
- ³ -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWN: M. YOUNGER 21FEB2012		MATERIAL: -		HEAT TREAT: -																
CHK: B.A.WOLFE 22FEB2012		APVD: B.A. WOLFE 22FEB2012		 TE Connectivity																
NAME: B.A. WOLFE		SCALE: -																		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SURFACE TEXTURE: 																
<table border="1" style="font-size: small;"> <tr><td>0</td><td>PLC</td><td>± .-</td></tr> <tr><td>1</td><td>PLC</td><td>± .-</td></tr> <tr><td>2</td><td>PLC</td><td>± .-</td></tr> <tr><td>3</td><td>PLC</td><td>± .-</td></tr> <tr><td>4</td><td>PLC</td><td>± .-</td></tr> </table>		0	PLC	± .-	1	PLC	± .-	2	PLC	± .-	3	PLC	± .-	4	PLC	± .-	ANGLES: -		DRAWING NO: 1583004	
0	PLC	± .-																		
1	PLC	± .-																		
2	PLC	± .-																		
3	PLC	± .-																		
4	PLC	± .-																		
P LTR		REVISION RECORD		DATE DWN APVD																
- SEE SHEET 1		-		-																
3308-8 (3/11)		8		7																
		6		5																
		4		3																
		2		1																
LOC: A		DIST: 00		SHEET: 2 of 2																

THIS DRAWING IS A CONTROLLED DOCUMENT. DRAW NO 1583004

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE. IT IS TO BE KEPT CONFIDENTIAL AND PROPRIETARY AND NOT TO BE DISCLOSED TO ANY OTHER PERSONNEL WITHOUT AUTHORIZATION FROM TE. www.te.com