

SIMATIC S7-1200, DIGITAL INPUT SB 1221, 4DI, 5VDC 200KHZ, SOURCE



Figure similar

Input current	
from backplane bus 5 V DC, typ.	50 mA
Output voltage	
Power supply to the transmitters	
• Supply current, max.	4 mA; per channel
Power loss	
Power loss, typ.	1 W
Digital inputs	
Number of digital inputs	4; Current-sourcing
• in groups of	1
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	4
Input voltage	
• Type of input voltage	DC
• Rated value (DC)	5 V

• for signal "0"	0 to 1 V
• for signal "1"	2 to 6 V
Input current	
• for signal "0", max. (permissible quiescent current)	3 mA
• for signal "1", min.	6 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
— at "0" to "1", max.	2 µs
for interrupt inputs	
— parameterizable	Yes
for counter/technological functions	
— parameterizable	Yes
Cable length	
• shielded, max.	50 m; shielded, twisted pair
Digital outputs	
Number of digital outputs	0
Short-circuit protection	No
Interrupts/diagnostics/status information	
Alarms	Yes
Diagnostic functions	Yes
Diagnostics indication LED	
• for status of the inputs	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in dispatch package
Ambient temperature during operation	
• permissible temperature range	-20 °C to +60 °C horizontal mounting, -20 °C to 50 °C vertical mounting, 95% humidity, non-condensing
• min.	-20 °C
• max.	60 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Storage/transport, min.	660 hPa

• Storage/transport, max.	1 080 hPa
Relative humidity	
• permissible range (without condensation) at 25 °C	95 %
Mechanics/material	
Enclosure material (front)	
• Plastic	Yes
Dimensions	
Width	38 mm
Height	62 mm
Depth	21 mm
Weights	
Weight, approx.	40 g
last modified:	22.01.2016