

132-00011



Article Number: 132-00011

Button Head Tie, 105lb, 15.0", Max Bundle Diameter 4.3" PA66HIRHSUV, PA66HS, Black, 50/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 132-00011

Type BT105L

Color Black (BK)

Features and Benefits

- Unique two piece tie allows parallel entry and exit through the head for easy assembly.
- High impact, heat stabilized material gives strength needed for trucking and heavy equipment applications.

Product Description The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides, and has two opposed pawls recessed within a domed head. This design allows the strap to be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.

Short Description Button Head Tie, 105lb, 15.0", Max Bundle Diameter 4.3" PA66HIRHSUV, PA66HS, Black, 50/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 105.0 lbs

Minimum Tensile Strength (Metric) 467 N

Length L (Imperial) 15.0 "

Length L (Metric) 381.5 mm

Fixation Method Connector Clip

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.22 "

Width W (Metric) 5.6 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 4.3 "

Bundle Diameter Max. (Metric) 110.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 50

Carton Quantity 1000

Material and Specifications

Material Polyamide 6.6 heat stabilized (PA66HS)
Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HS

PA66HIRHSUV

Material Cable Tie Polyamide 6.6 high impact modified, heat and UV-resistant (PA66HIRHSUV)

Flammability UL94 HB

Material Head Polyamide 6.6 heat stabilized (PA66HS)

Operating Temperature -40°F to +230°F (-40°C to +110°C)
-40°F to +221°F (-40°C to +105°C)