

211-60001



Article Number: 211-60001

P Clamp, .39" Width, .2" Max Bundle Dia, .17" Mounting Hole Dia, PA66HS, Black, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 211-60001

Type H2P

Color Black (BK)

Features and Benefits

- P-Clamps easily guide and locate wire and cables up to 1" in diameter.
- Designed with a radiused edge to prevent chaffing and cutting into insulation.

Product Description HellermannTyton P Clamps easily guide and locate wires and cables. The clamps are designed with a radiused edge to prevent chaffing and cutting into insulation. Available sizes up to 1" bundle diameters.

Short Description P Clamp, .39" Width, .2" Max Bundle Dia, .17" Mounting Hole Dia, PA66HS, Black, 100/pkg

Product Dimensions

Fixation Method screw-hole

Variant Closed

Width W (Imperial) 0.39 "

Width W (Metric) 10.0 mm

Bundle Diameter Max. (Imperial) 0.2 "

Bundle Diameter Max. (Metric) 5.0 mm

Mounting Hole Diameter D (Imperial) 0.17 "

Mounting Hole Diameter D (Metric) 4.2 mm

Nominal Diameter (Imperial) 3/16 "

Nominal Diameter (Metric) 5 mm

Wall Thickness WT (Imperial) .03937 "

Wall Thickness WT (Metric) 1.0 mm

Mounting Hole Centers (Imperial) 0.37 "

Mounting Hole Diameter D Max. 4.2 mm

(Metric) Mounting Hole Diameter D Min. (Metric) 4.2 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100 Pieces

Carton Quantity 6000 Pieces

Weight (Metric) 0.4 kg

Material and Specifications

Material Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut PA66HS
Flammability UL94 V2
Operating Temperature -40°F to +221°F (-40°C to +105°C)
ROHS Compliant Yes