


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED



NOTES:
 1. MATERIAL:
 BNC MALE: : BRASS, NICKEL PLATED
 BODY : BRASS, NICKEL PLATED
 CENTER PIN : BRASS, GOLD PLATED
 CABLE: RG174/U
 COLOR IS BLACK

THE TOLERANCE IS:
 <1000 ±5
 ≥1000 ±10



No.	ACD No.	L(mm)	TITLE
12	CO-174BNCX200-025	7625	CA BNC M/BNC M RG174/U 25'
11	CO-174BNCX200-015	4575	CA BNC M/BNC M RG174/U 15'
10	CO-174BNCX200-012	3660	CA BNC M/BNC M RG174/U 12'
9	CO-174BNCX200-010	3050	CA BNC M/BNC M RG174/U 10'
8	CO-174BNCX200-007.5	2286	CA BNC M/BNC M RG174/U 7.5'
7	CO-174BNCX200-005	1525	CA BNC M/BNC M RG174/U 5'
6	CO-174BNCX200-004	1220	CA BNC M/BNC M RG174/U 4'
5	CO-174BNCX200-003	915	CA BNC M/BNC M RG174/U 3'
4	CO-174BNCX200-002.5	762	CA BNC M/BNC M RG174/U 2.5'
3	CO-174BNCX200-002	610	CA BNC M/BNC M RG174/U 2'
2	CO-174BNCX200-001.5	457	CA BNC M/BNC M RG174/U 1.5'
1	CO-174BNCX200-001	305	CA BNC M/BNC M RG174/U 1'

UNLESS OTHERWISE SPECIFIED EAR N.D.
 DIMENSIONS ARE IN INCHES
 TOLERANCES ARE:
 DECIMALS .015 .010 .005 .0025
 .0015 .0010 .0005 .00025
 .00015 .00010 .00005 .000025

APPROVALS	DATE	APPROVALS	DATE
DESIGNED	2006-11-18	CHECKED	
DRAWN		RESP. ENG.	
		MFG. ENG.	

THIRD ANGLE PROJECTION	SIZE DWG. NO.	SCALE	SHEET	OF
	A			

NOTES: UNLESS OTHERWISE SPECIFIED

Amphenol Cables on Demand
 20 VALLEY ST. ENDICOTT, NY 13760
 TWO IN-LINE BNC (MOST POPULAR)
 CO-174BNCX200-XXX