


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED



MATERIAL:
 SMA: BODY: BRASS, GOLD-PLATED,
 CENTER PIN: BRASS, GOLD-PLATED,
 CABLE: RG174/U
 THE TOLERANCE IS: <1000 ±5
 >=1000 ±10



No.	ACD No.	L(mm)	TITLE
5	CO-174RASMAX2-005	1525	CA SMA M RAS/MAM RA RG174/U 5'
4	CO-174RASMAX2-002.5	762	CA SMA M RAS/MAM RA RG174/U 2.5'
3	CO-174RASMAX2-001.5	457	CA SMA M RAS/MAM RA RG174/U 1.5'
2	CO-174RASMAX2-001	305	CA SMA M RAS/MAM RA RG174/U 1'
1	CO-174RASMAX2-000.6	152	CA SMA M RAS/MAM RA RG174/U 6"

UNLESS OTHERWISE SPECIFIED		EAS NO.	
DIMENSIONS ARE IN INCHES		DATE	
TOLERANCES ARE:		2006-11-18	
DECIMALS	ANGLES	APPROVALS	DATE
.X	± X	DRAWN/	
.XX	± XX	CHECKED	
.XXX	± XXX	RESP ENG	
THIRD ANGLE PROJECTION		MPG ENG	

TWO RIGHT ANGLE SMA

Amphenol Cables on Demand
 20 VALLEY ST. ENDICOTT, NY 13760

NOTES: UNLESS OTHERWISE SPECIFIED

CAD FILE:	SIZE DWG. NO.	REV.
	A	CO-174RASMAX2-XXX.X
	SCALE	SHEET OF