

# Magic Rubber

Fast cross linking bicomponent rubber

Bicomponent insulating liquid rubber, extremely conformable and fluid, flexible, elastic and re-enterable. In just a few minutes, transforms into a rubber with very high dielectric, thermal, mechanical and elastic characteristics.

- Cross linking time:**  
15 minutes at 23°C
- Volume resistivity:**  
>2 10<sup>15</sup> Ω cm
- Dielectric strength:**  
> 23 kV/mm
- Specific weight:**  
1,22 approx
- Degree of protection:**  
IP68 (in proper casings)

- For installation up to 1kV
- Low smoke, toxic and corrosive gas emissions
- Ideal also for casts and moulds
- Non toxic and safe
- No shelf life



## Magic Rubber & Rubber Fluid

Product	Colour	Package type	Total quantity
Magic Rubber 500	●	2 bicomponent bottles 1 measuring cup - 1 mixing palette	500 gr
Magic Rubber 10	●	2 bicomponent tanks 1 measuring cup - 1 mixing palette	10 kg
Rubber Fluid 200	●	Bicomponent single dose bags	200 gr
Rubber Fluid 350	●	Bicomponent single dose bags	350 gr



Mix the 2 components in a ratio of 1:1.



Mix for max 30".



Pour the product into the casing to be filled.



In just a few minutes, the product transforms into rubber.