

## MMB.50C2



Article Number: 151-00116

Masonry Mount, 1.24" Length, .25" Hole Dia., .18" Max. Cable Tie Width, PA46, Black, 100/pkg



Download spec sheet

### Base Data

Local Order Number MMB.50C2

Type MMB.5

Color Black (BK)

**Features and Benefits**

- Masonry Mounts provides a permanent solution when fastening wire and cables to masonry surfaces.
- The mounts have easy installation into predrilled holes allowing for faster use.

**Product Description** HellermannTyton masonry mounts provide a permanent mounting solution when fastening wire and cables to masonry surfaces. Designed for easy installation by simply tapping into predrilled holes.

**Short Description** Masonry Mount, 1.24" Length, .25" Hole Dia., .18" Max. Cable Tie Width, PA46, Black, 100/pkg

### Product Dimensions

Length L (Imperial) 1.24 "

Length L (Metric) 31.5 mm

Fixation Method with Fir Tree (Mounts)

Width W (Imperial) 0.375 "

Width W (Metric) 9.5 mm

Cable Tie Width Max. (Imperial) 0.18 "

Cable Tie Width Max. (Metric) 4.6 mm

Width W2 (Imperial) 0.22 "

Width W2 (Metric) 5.6 mm

Width W3 (Imperial) 0.308 "

Width W3 (Metric) 7.8 mm

Height H (Imperial) 0.37 "

Height H (Metric) 9.4 mm

Mounting Hole Diameter D (Imperial) 0.25 "

Mounting Hole Diameter D (Metric) 6.35 mm

Mounting Hole Diameter D Max. 6.35 mm

(Metric) Mounting Hole Diameter D Min. (Metric) 6.35 mm

### Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 9000

### Material and Specifications

---

**Material** Polyamide 4.6 (PA46)  
**Material Shortcut** PA46  
**Flammability** UL94 V2  
**Operating Temperature** -40°F to +275°F (-40°C to +135°C)  
**ROHS Compliant** Yes