

PBM10C2



Article Number: 151-00230

Push Mount, .25" Hole Dia., .12" Max Panel, .2" Max Tie Width, PA66, White, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number PBM10C2

Type PBM

Color White (WH)

- Features and Benefits**
- Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel.
 - The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.

Product Description HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.

Short Description Push Mount, .25" Hole Dia., .12" Max Panel, .2" Max Tie Width, PA66, White, 100/pkg

Product Dimensions

Width W (Imperial) 0.26 "

Width W (Metric) 6.6 mm

Cable Tie Width Max. (Imperial) 0.2 "

Cable Tie Width Max. (Metric) 5.0 mm

Height H (Imperial) 0.4 "

Height H (Metric) 10.2 mm

Height H2 (Imperial) 0.08 "

Height H2 (Metric) 2.0 mm

Panel Thickness Max. (Imperial) 0.12 "

Panel Thickness Max. (Metric) 3.0 mm

Mounting Hole Diameter D (Imperial) 0.25 "

Mounting Hole Diameter D (Metric) 6.35 mm

Mounting Hole Diameter D Max. (Imperial) 0.29 "

Mounting Hole Diameter D Max. (Metric) 6.4 mm

Mounting Hole Diameter D Min. (Metric) 6.35 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 15000

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL94 V2

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

Certification/Specification UL

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes