

## RT50LL9C2

**Article Number: 115-06102**

**Releasable Cable Tie, 15" Long, 50 lb Tensile Strength, PA66, Natural, 100/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** RT50LL9C2  
**Type** RT50LL  
**Color** Natural (NA)

**Features and Benefits**

- Special design offers a release feature for quick and easy access to wire bundles.
- Head design provides high tensile strength with very low insertion force even after repeated use.
- Bent tail ensures a quick and simple installation.

**Product Description** HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Releasable Cable Tie, 15" Long, 50 lb Tensile Strength, PA66, Natural, 100/pkg

### Product Dimensions

**Minimum Tensile Strength (Imperial)** 50.0 lbs

**Minimum Tensile Strength (Metric)** 225.0 N

**Length L (Imperial)** 15.0 "

**Length L (Metric)** 380.0 mm

**Fixation Method** None

**Identification Plate Position** none

**Releasable Closure** Yes

**Tie Closure** plastic pawl

**Variant** Inside Serrated

**Width W (Imperial)** 0.18 "

**Width W (Metric)** 4.6 mm

**Bundle Diameter Min. (Imperial)** 0.06 "

**Bundle Diameter Min. (Metric)** 1.5 mm

**Bundle Diameter Max. (Imperial)** 4.0 "

**Bundle Diameter Max. (Metric)** 101.0 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 100

**Carton Quantity** 5000

### Material and Specifications

---

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL94 V2
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL
<b>UL Listed (US and Canada)</b>	No
<b>UL Recognized (US and Canada)</b>	Yes