

## SNP110C2



Article Number: 190-00022

Snapper Hose Clamps, .237"/.264" Min/Max Diameter, POM, White, 100/pkg



Download spec sheet

### Base Data

**Local Order Number** SNP110C2  
**Type** SNP1  
**Color** White (WH)

**Features and Benefits**

- Designed for quick, ratcheted installation and can be released and reused.
- Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.

**Product Description** HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

**Short Description** Snapper Hose Clamps, .237"/.264" Min/Max Diameter, POM, White, 100/pkg

### Product Dimensions

**Fixation Method** Plug-in mounting  
**Variant** Closed  
**Width W2 (Imperial)** 0.148 "  
**Width W2 (Metric)** 3.76 mm  
**Bundle Diameter Min. (Imperial)** 0.3 "  
**Bundle Diameter Min. (Metric)** 6.0 mm  
**Bundle Diameter Max. (Imperial)** 0.26 "  
**Bundle Diameter Max. (Metric)** 6.5 mm  
**Diameter Min. (Imperial)** 0.237 "  
**Diameter Min. (Metric)** 6.02 mm  
**Diameter Max. (Imperial)** 0.264 "  
**Diameter Max. (Metric)** 6.71 mm  
**Nominal Diameter (Imperial)** 1/4 "  
**Nominal Diameter (Metric)** 6 mm  
**Wall Thickness WT (Imperial)** 0.04 "  
**Wall Thickness WT (Metric)** 1.0 mm

### Logistics and Packaging

**Quantity Per** bag  
**Package Quantity (Metric)** 100 Pieces  
**Carton Quantity** 25000

### Material and Specifications

**Material** Polyacetal (POM)  
**Material Shortcut** POM  
**Flammability** UL94 HB  
**Operating Temperature** -40°F to +185°F (-40°C to +85°C)  
**ROHS Compliant** Yes