

SNP22GHS0C2



Article Number: 192-10220

Snapper Hose Clamps, .933"/1.079" Min/Max Diameter, PA66GF13%, Black, 100/pkg

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	SNP22GHS0C2
Type	SNP22
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none">• Designed for quick, ratcheted installation and can be released and reused.• Heat stabilized material is suitable for high temperature applications.
Product Description	HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.
Short Description	Snapper Hose Clamps, .933"/1.079" Min/Max Diameter, PA66GF13%, Black, 100/pkg

Product Dimensions

Fixation Method	Plug-in mounting
Variant	Closed
Width W2 (Imperial)	0.236 "
Width W2 (Metric)	5.99 mm
Bundle Diameter Min. (Imperial)	0.93 "
Bundle Diameter Min. (Metric)	23.7 mm
Bundle Diameter Max. (Imperial)	1.08 "
Bundle Diameter Max. (Metric)	27.4 mm
Diameter Min. (Imperial)	0.933 "
Diameter Min. (Metric)	23.7 mm
Diameter Max. (Imperial)	1.079 "
Diameter Max. (Metric)	27.41 mm
Nominal Diameter (Imperial)	1 "
Nominal Diameter (Metric)	26 mm
Wall Thickness WT (Imperial)	0.071 "
Wall Thickness WT (Metric)	1.8 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100 Pieces
Carton Quantity	2000
Weight (Metric)	0.34 kg

Material and Specifications

Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
Material Shortcut	PA66GF13
Flammability	UL94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes