HellermannTyton

SNP710C2

tum

Article Number: 190-00204

Snapper Hose Clamps, .456"/.56" Min/Max Diameter, POM, White, 100/pkg

RoHS



Base Data

Local Order Number SNP710C2

Type SNP7

Color White (WH)

Features and Benefits • Designed for quick, ratcheted installation and can be released and reused.

· Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.

Product Description HellemannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time.

The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high

performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

Short Description Snapper Hose Clamps, .456"/.56" Min/Max Diameter, POM, White, 100/pkg

Product Dimensions

Fixation Method Plug-in mounting

Variant Closed

Width W2 (Imperial) 0.232 "

Width W2 (Metric) 5.89 mm

Diameter Min. (Imperial) 0.456 "

Diameter Min. (Metric) 11.58 mm

Diameter Max. (Imperial) 0.56 "

Diameter Max. (Metric) 14.22 mm

Wall Thickness WT (Imperial) 0.069 "

Wall Thickness WT (Metric) 1.8 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 6000

Material and Specifications

Material Polyacetal (POM)

Material Shortcut POM

Flammability UL94 HB

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

